



ITC

| Model*                                                       | SN9ITC-DW                      | SN7ITC-DW  | SN5ITC-DW  | SN4ITC-DW  |
|--------------------------------------------------------------|--------------------------------|------------|------------|------------|
| Device Configurations                                        |                                |            |            |            |
| Battery                                                      | 312                            |            |            |            |
| Control options                                              | Push button and Volume Control |            |            |            |
| Receiver options                                             | LP, MP, HP, UP                 |            |            |            |
| IP Classification                                            | IP68                           |            |            |            |
| Audiological Features                                        |                                |            |            |            |
| Channels                                                     | 17                             | 14         | 12         | 12         |
| Autoscope Adaptive Directionality                            | ●                              | –          | –          | –          |
| Adjustable directional mix                                   | ●                              | –          | –          | –          |
| Multiscope Adaptive Directionality                           | –                              | ●          | –          | –          |
| Adaptive directionality                                      | –                              | –          | ●          | ●          |
| Soft Switching                                               | ●                              | ●          | ●          | ●          |
| Streaming Bass Boost                                         | 3 settings                     | 3 settings | 2 settings | 2 settings |
| Environmental Optimiser II                                   | ●                              | –          | –          | –          |
| Environmental Optimiser I                                    | –                              | ●          | ●          | ●          |
| Noise Tracker II                                             | 5 settings                     | 4 settings | 3 settings | 2 settings |
| Expansion                                                    | 3 settings                     | 3 settings | 2 settings | 2 settings |
| Impulse Noise Reduction                                      | 3 settings                     | 3 settings | 2 settings | 2 settings |
| Wind Guard                                                   | 3 settings                     | 3 settings | 2 settings | 2 settings |
| Sound Shaper                                                 | ●                              | ●          | ●          | ●          |
| DFS Ultra III (w/ Music Mode)                                | ●                              | ●          | ●          | ●          |
| Synchronised Acceptance Manager                              | ●                              | ●          | ●          | ●          |
| Low Frequency Boost**                                        | ●                              | ●          | ●          | ●          |
| Amplification Strategy (WDRC/Semi-Linear/Linear)**           | ●                              | ●          | ●          | ●          |
| Tinnitus Sound Generator                                     | ●                              | ●          | ●          | ●          |
| Functional Features                                          |                                |            |            |            |
| Ear to Ear Communication (Controls only)                     | ●                              | ●          | ●          | ●          |
| Bluetooth® Auracast™                                         | ●                              | ●          | ●          | ●          |
| Direct audio streaming (compatible iOS and Android™ devices) | ●                              | ●          | ●          | ●          |
| TV-Streamer+, Multi-Mic+ and Remote Control                  | ●                              | ●          | ●          | ●          |
| ReSound Smart 3D™ app                                        | ●                              | ●          | ●          | ●          |
| Sound Enhancer (ReSound Smart 3D™ app)                       | ●                              | –          | –          | –          |
| Remote Fine Tuning and Updates                               |                                |            |            |            |
| ReSound Assist                                               | ●                              | ●          | ●          | ●          |
| ReSound Assist Live                                          | ●                              | ●          | ●          | ●          |
| Remote Firmware Updates                                      | ●                              | ●          | ●          | ●          |
| Fitting Features                                             |                                |            |            |            |
| Fitting Software ReSound Smart Fit™ 2.4 or higher            | ●                              | ●          | ●          | ●          |
| Fully Flexible Programs                                      | 4                              | 4          | 4          | 4          |
| Auto DFS                                                     | ●                              | ●          | ●          | ●          |
| Datalogging                                                  | ●                              | ●          | ●          | ●          |
| Wireless Fitting with Noahlink Wireless                      | ●                              | ●          | ●          | ●          |

\* Availability of models may vary by country.  
\*\* Only available for UP receiver.



© 2026 GN Hearing A/S. All rights reserved. ReSound is a trademark of GN Hearing A/S. Apple, the Apple logo, iPhone and iPad are trademarks of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google LLC. The Bluetooth word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. The Auracast word mark is a trademark owned by Bluetooth SIG, Inc.

403074000GB-26.08-Rev.C

Worldwide Headquarters  
GN Hearing A/S  
Lautrupbjerg 7  
DK-2750 Ballerup  
Denmark  
Tel.: +45 4575 1111  
resound.com

CVR no. 55082715

United Kingdom  
GN Hearing UK Ltd.  
Unit 13  
Talisman Business Centre  
Bicester  
Oxon OX26 6HR  
Tel: +44 1869 352800  
resound.com

Australia  
GN Hearing Australia Pty Ltd  
Suite 1001, Level 1  
1 Julius Avenue  
North Ryde, NSW 2113  
Tel.: (free) 1800 658 955  
www.gnhearing.com/en-au/



New Zealand  
GN Hearing New Zealand Limited  
4 Fred Thomas Drive  
Takapuna, Auckland, 0622  
Tel.: (free) 0800 900 126  
www.gnhearing.com/en-nz/

Technical Specifications


|                                                             |             | LP                                                 | MP                                                 |           |
|-------------------------------------------------------------|-------------|----------------------------------------------------|----------------------------------------------------|-----------|
|                                                             |             | ANSI S3.22-2014<br>IEC 60118-0:2022<br>2cc coupler | ANSI S3.22-2014<br>IEC 60118-0:2022<br>2cc coupler |           |
| Reference test gain (60 dB SPL input)                       | HFA         | 31                                                 | 36                                                 | dB        |
| Full-on gain (50 dB SPL input)                              | Max.<br>HFA | 40<br>37                                           | 50<br>45                                           | dB        |
| Maximum output (90 dB SPL input)                            | Max.<br>HFA | 113<br>108                                         | 115<br>113                                         | dB<br>SPL |
| Total harmonic distortion                                   | 500 Hz      | 1.3                                                | 0.6                                                | %         |
|                                                             | 800 Hz      | 1.3                                                | 0.8                                                |           |
|                                                             | 1600 Hz     | 1.0                                                | 0.5                                                |           |
|                                                             | 3200 Hz     | 0.2                                                | 0.2                                                |           |
| Equivalent input noise                                      |             | 23                                                 | 23                                                 | dB<br>SPL |
| Frequency range                                             |             | ≤200 - ≥8000                                       | ≤200 - ≥8000                                       | Hz        |
| Current Drain (Quiescent / Operating)<br>(Battery type 312) |             | 0.75 / 0.95                                        | 0.78 / 1.05                                        | mA        |

Patents pending.

All specifications are subject to change without notice.



■ LP  
■ MP





Technical Specifications

|                                                             |             | HP                                                 | UP                                                 |           |
|-------------------------------------------------------------|-------------|----------------------------------------------------|----------------------------------------------------|-----------|
|                                                             |             | ANSI S3.22-2014<br>IEC 60118-0:2022<br>2cc coupler | ANSI S3.22-2014<br>IEC 60118-0:2022<br>2cc coupler |           |
| Reference test gain (60 dB SPL input)                       | HFA         | 41                                                 | 46                                                 | dB        |
| Full-on gain (50 dB SPL input)                              | Max.<br>HFA | 60<br>54                                           | 68<br>61                                           | dB        |
| Maximum output (90 dB SPL input)                            | Max.<br>HFA | 120<br>118                                         | 128<br>123                                         | dB<br>SPL |
| Total harmonic distortion                                   | 500 Hz      | 0.6                                                | 0.3                                                | %         |
|                                                             | 800 Hz      | 1.1                                                | 0.6                                                |           |
|                                                             | 1600 Hz     | 0.2                                                | 0.2                                                |           |
|                                                             | 3200 Hz     | 0.1                                                | 0.0                                                |           |
| Equivalent input noise                                      |             | 23                                                 | 23                                                 | dB<br>SPL |
| Frequency range                                             |             | ≤200 - 6980                                        | ≤200 - 5350                                        | Hz        |
| Current Drain (Quiescent / Operating)<br>(Battery type 312) |             | 0.75 / 1.01                                        | 0.78 / 0.91                                        | mA        |

Patents pending.

All specifications are subject to change without notice.



■ HP  
■ UP

